

# **Sterra™ portfolio**

Overview of carbon emissions  
reduction potential



## Recycled engineering plastics for a more sustainable future



Recycled engineering plastics significantly contribute to reducing carbon footprints by lowering the demand for virgin plastic production, which is energy-intensive and generates high levels of greenhouse gas emissions. A circular approach minimizes waste sent to landfills, decreasing methane emissions and helps reduce the carbon footprint that is associated with plastic disposal even further.

Moreover, using recycled plastics in engineering applications can offer the same performance as new materials, fostering a more sustainable manufacturing cycle and contributing to a cleaner, greener environment.

### **Statera™ and Sterra™**

Mitsubishi Chemical Group has introduced its Statera™ offering of circular solutions including the Sterra™ portfolio of engineering polymer products with recycled content, which contribute to considerable carbon footprint reduction.




# Sterra™ portfolio – Overview

AEP*	GEP*	Polyethelene*
<b>Ketron™ Sterra™ CA30 PEEK</b> 70% recycled content 38% reduced Product Carbon Footprint	<b>Acetron™ C Sterra™ POM-C black</b> 100 % recycled content 77% reduced Product Carbon Footprint	<b>TIVAR™ Sterra™ UHMW-PE green</b> 70% recycled content 51% reduced Product Carbon Footprint
<b>Ketron™ Sterra™ HPV PEEK</b> 70% recycled content 47% reduced Product Carbon Footprint	<b>Ertalyte™ Sterra™ PET-P black</b> 100 % recycled content 63% reduced Product Carbon Footprint	<b>TIVAR™ Sterra™ ESD UHMW-PE</b> 70% recycled content 50% reduced Product Carbon Footprint
<b>Ketron™ Sterra™ 1000 PEEK</b> 25% recycled content 24% reduced Product Carbon Footprint		<b>TIVAR™ Sterra™ DrySlide UHMW-PE</b> 70% recycled content 50% reduced Product Carbon Footprint

\* Reduced carbon footprint values based on comparison with MCAM’s manufactured material using 100% virgin resin.


## Ketron™ Sterra™ 1000 PEEK vs. Ketron™ 1000 PEEK\*



### Ketron™ Sterra™ 1000 PEEK:

- 25% recycled content (post industrial material)
- ISO 14040/44 (ISO, 2006; ISO/TC, 2006) conform LCA study
- System boundary: Cradle to gate
- LCA results/background values are global averages and may be based on a varying number of manufacturing locations, incl. single location.
- A mass balance method according to ISCC PLUS standards is applied; certification is in place
- Mitsubishi Chemical Advanced Materials production sites for the manufacturing of this material are certified according to ISO 9001:2015 and ISO 14001:2015; production sites are using electricity from Renewable Sources (RE).

## Ketron™ Sterra™ CA30 PEEK vs. Ketron™ CA30 PEEK\*




\* Results based on comparison with MCAM's manufactured material using 100% virgin resin.  
Measured unit: 1 kg of product

### Ketron™ Sterra™ CA30 PEEK:

- 70% recycled content (post industrial material)
- ISO 14040/44 (ISO, 2006; ISO/TC, 2006) conform LCA study
- System boundary: Cradle to gate
- LCA results/background values are global averages and may be based on a varying number of manufacturing locations, incl. single location.
- A mass balance method according to ISCC PLUS standards is applied; certification is in place
- Mitsubishi Chemical Advanced Materials production sites for the manufacturing of this material are certified according to ISO 9001:2015 and ISO 14001:2015; production sites are using electricity from Renewable Sources (RE).



## Ketron™ Sterra™ HPV PEEK vs. Ketron™ HPV PEEK\*




\* Results based on comparison with MCAM's manufactured material using 100% virgin resin.  
Measured unit: 1 kg of product

### Ketron™ Sterra™ HPV PEEK

- 70% recycled content (post industrial material)
- ISO 14040/44 (ISO, 2006; ISO/TC, 2006) conform LCA study
- System boundary: Cradle to gate
- LCA results/background values are global averages and may be based on a varying number of manufacturing locations, incl. single location.
- A mass balance method according to ISCC PLUS standards is applied; certification is in place
- Mitsubishi Chemical Advanced Materials production sites for the manufacturing of this material are certified according to ISO 9001:2015 and ISO 14001:2015; production sites are using electricity from Renewable Sources (RE).

## Ertalyte™ Sterra™ PET-P vs. Ertalyte™ PET-P\*




\* Results based on comparison with MCAM's manufactured material using 100% virgin resin.  
Measured unit: 1 kg of product

### Ertalyte™ Sterra™ PET-P:

- 100% recycled content (post industrial material)
- ISO 14040/44 (ISO, 2006; ISO/TC, 2006) conform LCA study
- System boundary: Cradle to gate
- LCA results/background values are global averages and may be based on a varying number of manufacturing locations, incl. single location.
- A mass balance method according to ISCC PLUS standards is applied; certification is in place
- Mitsubishi Chemical Advanced Materials production sites for the manufacturing of this material are certified according to ISO 9001:2015 and ISO 14001:2015; production sites are using electricity from Renewable Sources (RE).

## Acetron™ C Sterra™ POM-C vs. Ertacetal™ C POM-C\*




\* Results based on comparison with MCAM's manufactured material using 100% virgin resin.  
Measured unit: 1 kg of product

### Acetron™ Sterra™ POM-C:

- 100% recycled content (post industrial material)
- ISO 14040/44 (ISO, 2006; ISO/TC, 2006) conform LCA study
- System boundary: Cradle to gate
- LCA results/background values are global averages and may be based on a varying number of manufacturing locations, incl. single location.
- A mass balance method according to ISCC PLUS standards is applied; certification is in place
- Mitsubishi Chemical Advanced Materials production sites for the manufacturing of this material are certified according to ISO 9001:2015 and ISO 14001:2015; production sites are using electricity from Renewable Sources (RE).



## TIVAR™ Sterra™ UHMW-PE vs. TIVAR™ 1000 UHMW-PE\*




\* Results based on comparison with MCAM's manufactured material using 100% virgin resin.  
Measured unit: 1 kg of product

### TIVAR™ Sterra™ UHMW-PE:

- 70% recycled content (post industrial material)
- ISO 14040/44 (ISO, 2006; ISO/TC, 2006) conform LCA study
- System boundary: Cradle to gate
- LCA results/background values are global averages and may be based on a varying number of manufacturing locations, incl. single location.
- A mass balance method according to ISCC PLUS standards is applied; certification is in place
- DQS Certificate ([iscc-system.org](https://www.iscc-system.org))
- Mitsubishi Chemical Advanced Materials production sites for the manufacturing of this material are certified according to ISO 9001:2015 and ISO 14001:2015; production sites are using electricity from Renewable Sources (RE).


## TIVAR™ Sterra™ ESD UHMW-PE vs. TIVAR™ Antistatic UHMW-PE\*



### TIVAR™ Sterra™ ESD UHMW-PE:

- 70% recycled content (post industrial material)
- ISO 14040/44 (ISO, 2006; ISO/TC, 2006) conform LCA study
- System boundary: Cradle to gate
- LCA results/background values are global averages and may be based on a varying number of manufacturing locations, incl. single location.
- A mass balance method according to ISCC PLUS standards is applied; certification is in place
- DQS Certificate ([iscc-system.org](https://www.iscc-system.org))
- Mitsubishi Chemical Advanced Materials production sites for the manufacturing of this material are certified according to ISO 9001:2015 and ISO 14001:2015; production sites are using electricity from Renewable Sources (RE).

## TIVAR™ Sterra™ DrySlide UHMW-PE vs. TIVAR™ DrySlide UHMW-PE\*




\* Results based on comparison with MCAM's manufactured material using 100% virgin resin.  
Measured unit: 1 kg of product

### TIVAR™ Sterra™ DrySlide UHMW-PE:

- 70% recycled content (post industrial material)
- ISO 14040/44 (ISO, 2006; ISO/TC, 2006) conform LCA study
- System boundary: Cradle to gate
- LCA results/background values are global averages and may be based on a varying number of manufacturing locations, incl. single location.
- A mass balance method according to ISCC PLUS standards is applied; certification is in place
- DQS Certificate ([iscc-system.org](https://www.iscc-system.org))
- Mitsubishi Chemical Advanced Materials production sites for the manufacturing of this material are certified according to ISO 9001:2015 and ISO 14001:2015; production sites are using electricity from Renewable Sources (RE).


# Engineering Shapes & Solutions



\* Certifications specific to certain parts of the site.

\*\* MCAM Recycling Solutions

# Engineering Shapes & Solutions



Status: February 2025

# Get in touch

## Contact.

[contact.mcam@mcgc.com](mailto:contact.mcam@mcgc.com)

## Visit.

[www.mcam.com/en/contact](http://www.mcam.com/en/contact)

---

### Europe

Mitsubishi Chemical  
Advanced Materials NV  
Galgenveldstraat 12  
8700 Tielt,  
Belgium

**Tel: +32 51 42 35 11**

[www.mcam.com](http://www.mcam.com)

### North America

Mitsubishi Chemical  
Advanced Materials Inc.  
2120 Fairmont Avenue  
PO Box 14235 — Reading,  
PA 19612-4235, U.S.A.

**Tel: +1 610 320 6600**

### Asia-Pacific

Mitsubishi Chemical  
Advanced Materials Asia Pacific Ltd.  
Unit 7B, 35/F, Cable TV Tower,  
9 Hoi Shing Road,  
Tsuen Wan, Hong Kong

**Tel: +852 2470 26 83**

All statements, technical information, recommendations, and advice are for informational purposes only and are not intended and should not be construed as a warranty of any type or term of sale. The reader, however, is cautioned that Mitsubishi Chemical Advanced Materials

does not guarantee the accuracy or completeness of this information and it is the customer's responsibility to test and assess the suitability of the products of Mitsubishi Chemical Advanced Materials in any given application or for use in a finished device.

Statera™ and Sterra™ are protected trademarks of the Mitsubishi Chemical Advanced Materials group of companies. Design and content created by Mitsubishi Chemical Advanced Materials and protected by copyright law. Copyright © 2025 by Mitsubishi Chemical Advanced Materials. All rights reserved.

**Mitsubishi Chemical Advanced Materials AG**